



# Ceramalux Non-ALTO

## SON ALTO 250W LV E E39 CL SL/3

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Chromaticity Coordinate X (Nom)	523
Chromaticity Coordinate Y (Nom)	412
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	102 lm/W
Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	26
Operating and Electrical	
Power Consumption	251 W
Lamp Current (Nom)	3.0 A
Voltage (Nom)	95 V
Voltage (Nom)	95 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED18
Approval and Application	
Mercury (Hg) Content (Max)	23.5 mg
Product Data	
Order product name	C250S50 3PK
Full product name	SON ALTO 250W LV E E39 CL SL/3
Order code	140979
Material Nr. (12NC)	928601139404
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677253905
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677140972

# Ceramalux Non-ALTO

## Dimensional drawing

Product	D	C (max)
C250S50 3PK	57.2 mm	248 mm

