



# Ceramalux Instant Restrike

## C250S50/2 1/12PK

Dual arc-tube delivers 40,000 hour rated average life as compared to 24,000 hour rated average life for standards HPS lamps. Ideal for industrial applications, warehouses, post top applications and parking lots.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	521
Chromaticity Coordinate Y (Nom)	415
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	102.6 lm/W
Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	251 W
Lamp Current (Nom)	3 A
Voltage (Nom)	100 V

Voltage (Nom)	100 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED18
Approval and Application	
Mercury (Hg) Content (Nom)	47 mg
Product Data	
Order product name	C250S50/2 1/12PK
Full product name	C250S50/2 1/12PK
Order code	377176
Material Nr. (12NC)	928601145501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677377175

# Ceramalux Instant Restrike

Numerator - Packs per outer box	12
EAN/UPC - Case	50046677377170

## Dimensional drawing

Product	D	C (max)
C250S50/2 1/12PK	2.25 inch	9.75 inch

