



# Ceramalux Instant Restrike

# C150S55/2 1/12PK

Dual arc-tube delivers 40,000 hour rated average life as compared to 24,000 hour rated average life for standards HPS lamps. Ideal for industrial applications, warehouses, post top applications and parking lots.

### **Warnings and Safety**

- · Lamp contains mercury.
- · Manage in Accord with Disposal Laws.
- · See: www.lamprecycle.org or 1-800-555-0050

#### **Product data**

General Information		
Cap-Base	E39 [Single Contact Mogul Screw]	
Operating Position	UNIVERSAL [Any or Universal (U)]	
Light Technical		
Chromaticity Coordinate X (Nom)	514	
Chromaticity Coordinate Y (Nom)	424	
Correlated Color Temperature (Nom)	2100 K	
Luminous Efficacy (Rated) (Min)	96 lm/W	
Luminous Efficacy (rated) (Nom)	106 lm/W	
Color rendering index (CRI)	21	
Operating and Electrical		
Power Consumption	150.6 W	
Lamp Current (Nom)	3.2 A	
Voltage (Nom)	55 V	

Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED-23 1/2
Approval and Application	
Mercury (Hg) Content (Max)	34 mg
Product Data	
Order product name	C150S55/2 1/12PK
Full product name	C150S55/2 1/12PK
Order code	265611
Material Nr. (12NC)	928601145601
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677265618

Datasheet, 2023, April 14 data subject to change

## **Ceramalux Instant Restrike**

Numerator - Packs per outer box	12
EAN/UPC - Case	50046677265613

#### Dimensional drawing

Product	D	C (max)
C150S55/2 1/12PK	2.938 inch	7.75 inch



