



# Ceramalux Instant Restrike

## C100S54/2 1/12PK

Dual arc-tube delivers 40,000 hour rated average life as compared to 24,000 hour rated average life for standards HPS lamps. Ideal for industrial applications, warehouses, post top applications and parking lots.

### Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	520
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	84 lm/W
Luminous Efficacy (rated) (Nom)	93 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	100.4 W
Lamp Current (Nom)	2.1 A
Voltage (Nom)	55 V
Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED-23 1/2
Approval and Application	
Mercury (Hg) Content (Max)	44.4 mg
Product Data	
Order product name	C100S54/2 1/12PK
Full product name	C100S54/2 1/12PK
Order code	265603
Material Nr. (12NC)	928601145701
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677265601
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677265606

Ceramalux Instant Restrike

Dimensional drawing

Product	D	C (max)
C100S54/2 1/12PK	2.938 inch	7.75 inch

