



Switch Start Metal Halide Standard

MH250/U UPC 3PK

High performance, Long life and Superior light quality A compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

Product data

General Information	
Base	E39 [Single Contact Mogul Screw]
Operating Position	Universal [Universal]
Main Application	General and Street Lighting
Life to 50% Failures (Nom)	10000 h
ANSI Code HID	M58-/E
Footnotes HID 1	Requires a ballast specified or approved for Philips metal halide lamps, or one that is designed to operate all popular brands of metal halide lamps. 1000W types will operate from H36 conventional lag type ballast for Mercury Vapor lamps at ambient temperatures of 50 degrees F or higher. 1000W types must not be operated at 1500W. (377)
Footnotes HID 2	Rated life: Vertical +/- 15 degrees. Other positions 75% of vertical life. (385)
Footnotes HID 3	Vertical lumens. Horizontal lumens 6%–10% lower. (393)
Light Technical	
Color Code	640 [CCT of 4000K]
Luminous Flux (Rated) (Min)	19125 lm

Luminous Flux (Rated) (Nom)	21250 lm
Color Designation	Cool White (CW)
Design Mean Lumens	13500 lm
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.395
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (Rated) (Min)	76.5 lm/W
Luminous Efficacy (rated) (Nom)	85 lm/W
Color Rendering Index (Nom)	65

Operating and Electrical

Lamp Current (Nom)	2.1 A
Ignition Supply Voltage (Min)	350 V
Re-Ignition Time (Min) (Max)	8 min
Ignition Time (Max)	120 s
Voltage (Max)	148 V
Voltage (Min)	118 V
Voltage (Nom)	133 V

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

Switch Start Metal Halide Standard

Cap-Base Information	Brass [Brass Cap]
Bulb Material	Hard Glass

Approval and Application

Energy Saving Product	Not Applicable
Picogram Per Lumen Hour	215.1 pg/lm.h
Mercury (Hg) Content (Nom)	33 mg

Luminaire Design Requirements


Bulb Temperature (Max)	400 °C
Cap-Base Temperature (Max)	210 °C

Product Data

Order product name	MH250/U UPC 3PK
EAN/UPC - Product	046677253622
Order code	140822
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	3
Material Nr. (12NC)	928601150812
Net Weight (Piece)	0.001 kg

Warnings and Safety

Dimensional drawing



MH R 250W/640 E39 ED28 U

Product

MH250/U UPC 3PK

