

# Pulse Start Metal Halide Standard

## MS175/BU/PS 12PK

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

### Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]
Life to 50% Failures (Nom)	15,000 hour(s)

Light Technical	
Color Code	635 [CCT of 3500K]
Color Designation	White (WH)
Chromaticity Coordinate X (Nom)	395
Chromaticity Coordinate Y (Nom)	390
Luminous Efficacy (Rated) (Min)	82.3 lm/W
Luminous Efficacy (rated) (Nom)	91 lm/W
Color rendering index (CRI)	62

Operating and Electrical	
Lamp Current (Nom)	1.5 A

Voltage (Nom)	132 V
Voltage (Nom)	132 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED28

Approval and Application	
Mercury (Hg) Content (Nom)	23.5 mg


Product Data	
Order product name	MS175/BU/PS 12PK
Full product name	MS175/BU/PS 12PK
Order code	928601152103
Material Nr. (12NC)	928601152103

## Pulse Start Metal Halide Standard

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677276621
Numerator - Packs per outer box	12

EAN/UPC - Case	50046677276626
----------------	----------------

### Dimensional drawing



Product	D	C (max)
MS175/BU/PS 12PK	3.5 inch	8.313 inch

