



Switch Start Metal Halide Protected

MP400/BU 6 PK

An efficient, protected "O" rated lighting solution that is suitable for open-rated fixtures. Ideal for both indoor and outdoor applications.

Warnings and Safety

• R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data


General Information		Voltage (Nom)	
Cap-Base	EX39 [Exclusionary Mogul Screw]	135 V	
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]	Voltage (Nom)	135 V
Life to 50% Failures (Nom)	20,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	640 [CCT of 4000K]	Bulb Finish	Clear
Color Designation	Cool White (CW)	Bulb Material	Hard Glass
Chromaticity Coordinate X (Nom)	385	Bulb Shape	ED37
Chromaticity Coordinate Y (Nom)	390		
Correlated Color Temperature (Nom)	4000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	100 lm/W	Energy Saving Product	Not Applicable
Color rendering index (CRI)	65	Mercury (Hg) Content (Nom)	57 mg
Operating and Electrical		Product Data	
Lamp Current (Nom)	3.25 A	Order product name	MP400/BU 6 PK
		Full product name	MP400/BU 6 PK
		Order code	928601157903

Switch Start Metal Halide Protected

Material Nr. (12NC)	928601157903
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677133320
Numerator - Packs per outer box	6

EAN/UPC - Case	50046677133325
----------------	----------------

Dimensional drawing



Product	D	C (max)
MP400/BU 6 PK	4.625 inch	11.5 inch

