



# Pulse Start Metal Halide Protected

## MP400/BU/PS 6PK

Philips Protected Pulse Start Metal Halide “O” Rated Lamps are a better alternative to the standard switch start metal halide.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]
Life to 50% Failures (Nom)	20,000 hour(s)
Light Technical	
Color Code	635 [CCT of 3500K]
Color Designation	White (WH)
Chromaticity Coordinate X (Nom)	405
Chromaticity Coordinate Y (Nom)	398
Correlated Color Temperature (Nom)	3800 K
Luminous Efficacy (Rated) (Min)	95 lm/W
Luminous Efficacy (rated) (Nom)	100 lm/W

Color rendering index (CRI)	65
Operating and Electrical	
Lamp Current (Nom)	3.25 A
Voltage (Nom)	135 V
Voltage (Nom)	135 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED37

## Pulse Start Metal Halide Protected

### Approval and Application

Mercury (Hg) Content (Nom) 50 mg

### Product Data

Order product name MP400/BU/PS 6PK

Full product name MP400/BU/PS 6PK

Order code 133348

Material Nr. (12NC) 928601158102


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 046677133344

Numerator - Packs per outer box 6

EAN/UPC - Case 50046677133349

## Dimensional drawing



Product	D	C (max)
MP400/BU/PS 6PK	4.625 inch	11.5 inch

