



Switch Start Metal Halide Protected

MP250/BU 12PK

An efficient, protected "O" rated lighting solution that is suitable for open-rated fixtures. Ideal for both indoor and outdoor applications.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]
Life to 50% Failures (Nom)	10,000 hour(s)

Light Technical	
Color Code	640 [CCT of 4000K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	395
Chromaticity Coordinate Y (Nom)	395
Correlated Color Temperature (Nom)	3800 K
Luminous Efficacy (Rated) (Min)	77 lm/W
Luminous Efficacy (rated) (Nom)	86 lm/W
Color rendering index (CRI)	62

Operating and Electrical	
Lamp Current (Nom)	2.1 A
Voltage (Nom)	133 V
Voltage (Nom)	133 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED28

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	32 mg

Product Data	
Order product name	MP250/BU 12PK

Switch Start Metal Halide Protected

Full product name	MP250/BU 12PK
Order code	281246
Material Nr. (12NC)	928601161903
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677281243

Numerator - Packs per outer box	12
EAN/UPC - Case	50046677281248

Dimensional drawing

Product	D	C (max)
MP250/BU 12PK	3.5 inch	8.313 inch

