



Switch Start Metal Halide Protected

MP250/BU 12PK

An efficient, protected "O" rated lighting solution that is suitable for open-rated fixtures. Ideal for both indoor and outdoor applications.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data

General Information		Operating and Electrical	
Cap-Base	EX39 [Exclusionary Mogul Screw]	Lamp Current (Nom)	2.1 A
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]	Voltage (Nom)	133 V
Life to 50% Failures (Nom)	10,000 hour(s)	Voltage (Nom)	133 V
Light Technical		Mechanical and Housing	
Color Code	640 [CCT of 4000K]	Bulb Finish	Clear
Color Designation	Cool White (CW)	Bulb Material	Hard Glass
Chromaticity Coordinate X (Nom)	395	Bulb Shape	ED28
Chromaticity Coordinate Y (Nom)	395		
Correlated Color Temperature (Nom)	3800 K	Approval and Application	
Luminous Efficacy (Rated) (Min)	77 lm/W	Energy Saving Product	Not Applicable
Luminous Efficacy (rated) (Nom)	86 lm/W	Mercury (Hg) Content (Nom)	32 mg
Color rendering index (CRI)	62		
Product Data			
Order product name	MP250/BU 12PK		

Switch Start Metal Halide Protected

Full product name	MP250/BU 12PK
Order code	928601161903
Material Nr. (12NC)	928601161903
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677281243

Numerator - Packs per outer box	12
EAN/UPC - Case	50046677281248

Dimensional drawing

Product	D	C (max)
MP250/BU 12PK	3.5 inch	8.313 inch

