



MASTERColour CDM-T Elite MW

MASTERColour CDM-TMW Elite 210W/930 1CT

The medium wattage lighting system that gives superior, longer-lasting white light for both indoor and outdoor use

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing, except for protected versions with PGZX18 cap, which are designed for open luminaires (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	PGZ18
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	na [Not Applicable]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	30,000 hour(s)

Light Technical	
Color Code	930 [CCT of 3000K]
Luminous Flux	24,000 lm
Color Designation	Warm White (WW)
Saturated Red (R9)	50
Chromaticity Coordinate X (Nom)	0.434

Chromaticity Coordinate Y (Nom)	0.398
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (Rated) (Min)	105 lm/W
Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	90
Arc Length O (Nom)	12.1 mm


Operating and Electrical	
Power Consumption	210.0 W
Voltage (Nom)	100 V
Voltage (Nom)	100 V

MASTERColour CDM-T Elite MW

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	TMW28
Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) Content (Max)	24 mg
Energy Consumption kWh/1000 h	210 kWh
EPREL Registration Number	473296




Product Data	
Order product name	CDM-T Elite 210W/930 PGZ18.1CT/12
Full product name	MASTERColour CDM-TMW Elite 210W/930 1CT
Full product code	871829113950800
Order code	13950800
Material Nr. (12NC)	928601164731
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291139508
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291139515

Dimensional drawing



Product	D (max)	D	D	C (max)	C
CDM-T Elite 210W/930 PGZ18.1CT/12	29 mm	1.1 inch	28 mm	188 mm	186 mm

Photometric data




Light Distribution Diagram - CDM-T Elite 210W/930 PGZ18.1CT/12


Spectral Power Distribution Colour - CDM-T Elite 210W/930 PGZ18.1CT/12

MASTERColour CDM-T Elite MW

Lifetime



Life Expectancy Diagram - CDM-T Elite 210W/930 PGZ18.1CT/12



Lumen Maintenance Diagram - CDM-T Elite 210W/930 PGZ18.1CT/12

