



Energy Advantage CDM Lamps with Allstart Technology

CDM205/U/O/4K EA 130V 12/1

Philips Energy Advantage CDM lamps with AllStart Technology is a high-efficiency protected “O” rated CDM lighting solution that provides energy savings without compromising light quality.

Warnings and Safety

- R "WARNING:These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information			
Cap-Base	EX39 [Exclusionary Mogul Screw]	Saturated Red (R9)	40
Operating Position	UNIVERSAL [Any or Universal (U)]	Chromaticity Coordinate X (Nom)	0.381
Features	Energy Advantage AllStart	Chromaticity Coordinate Y (Nom)	0.384
Life to 50% Failures (Nom)	20,000 hour(s)	Luminous Efficacy (Rated) (Min)	88 lm/W
		Luminous Efficacy (rated) (Nom)	95 lm/W
		Color rendering index (CRI)	84
Light Technical		Operating and Electrical	
Color Code	841 [CCT of 4100K]	Lamp Current (Nom)	1.9 A
Color Designation	4100 Kelvin		

Energy Advantage CDM Lamps with Allstart Technology

Voltage (Nom)	128 V
Voltage (Nom)	128 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	ED28
Approval and Application	
Mercury (Hg) Content (Max)	38 mg
Product Data	
Order product name	CDM205/U/O/4K/EA/ED28

Full product name	CDM205/U/O/4K EA 130V 12/1
Order code	232561
Material Nr. (12NC)	928601166003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677232566
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677232561

Dimensional drawing



Product	D	D	L (min)	L (max)	L	C
CDM205/U/O/4K/EA/ED28	3.5 inch	3-1/2 inch	4-15/16 inch	5-1/8 inch	5 inch	8.313 inch

