



# Energy Advantage CDM Lamps with Allstart Technology

## CDM330/C/U/O/4K EA 130V 6/1

Philips Energy Advantage CDM lamps with AllStart Technology is a high-efficiency protected "O" rated CDM lighting solution that provides energy savings without compromising light quality.

#### Warnings and Safety

• R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

#### **Product data**

General Information				
Cap-Base	EX39 [Exclusionary Mogul Screw]			
Operating Position	UNIVERSAL [Any or Universal (U)]			
Features	Energy Advantage AllStart			
Life to 50% Failures (Nom)	24,000 hour(s)			
Light Technical				
Color Code	940 [CCT of 4000K]			
Color Designation	4000 Kelvin			
Saturated Red (R9)	75			
Chromaticity Coordinate X (Nom)	0.386			
Chromaticity Coordinate Y (Nom)	0.390			

Correlated Color Temperature (Nom)	3950 K		
Luminous Efficacy (Rated) (Min)	85 lm/W		
Luminous Efficacy (rated) (Nom)	94 lm/W		
Color rendering index (CRI)	86		
Operating and Electrical			
Lamp Current (Nom)	3.02 A		
Voltage (Nom)	130 V		
Voltage (Nom)	130 V		
Mechanical and Housing			
Bulb Finish	Coated glass		


Datasheet, 2023, April 14 data subject to change

## **Energy Advantage CDM Lamps with Allstart Technology**

Bulb Shape	ED37				
Approval and Application					
Mercury (Hg) Content (Max)	50 mg				
Product Data					
Order product name	330W ED37 CO Allstart 1SL				
Full product name	CDM330/C/U/O/4K EA 130V 6/1				

Order code	236935
Material Nr. (12NC)	928601166803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677236939
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677236934

### Dimensional drawing



Product	D (max)	D	L (max)	L	С
330W ED37 CO Allstart 1SL	118 mm	4.625 inch	184 mm	178 mm	11.5 inch

