



MASTERColour CDM-T Elite MW

CDM ELITE TMW 315/930/U/O EU

The medium wattage lighting system that gives superior, longer-lasting white light for both indoor and outdoor use

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing, except for protected versions with PGZX18 cap, which are designed for open luminaires (IEC61167, IEC 62035, IEC60598)
- $\boldsymbol{\cdot}$ The luminaire must be able to contain hot lamp parts if the lamp ruptures
- · Use only with electronic control gear
- · Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information			
Cap-Base	PGZX18. [PGZX18.]		
Operating Position	UNIVERSAL [Any or Universal (U)]		
Features	Protected (P)		
Flux measurement reference	Sphere		
Life to 50% Failures (Nom)	30,000 h		
Light Technical			
Color Code	930 [CCT of 3000K]		
Luminous Flux	36,200 lm		
Color Designation	Warm White (WW)		
Saturated Red (R9)	50		
Chromaticity Coordinate X (Nom)	0.434		

Chromaticity Coordinate Y (Nom)	0.398	
Correlated Color Temperature (Nom)	3000 K	
Luminous Efficacy (Rated) (Min)	105 lm/W	
Luminous Efficacy (rated) (Nom)	115 lm/W	
Color rendering index (CRI)	90	
Arc Length O (Nom)	16 mm	
Operating and Electrical		
Power Consumption	315.9 W	
Voltage (Nom)	100 V	
Voltage (Nom)	100 V	


Datasheet, 2023, April 16 data subject to change

MASTERColour CDM-T Elite MW

Controls and Dimension	
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T12 [38 mm (T12)]
Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) Content (Max)	28 mg
Energy Consumption kWh/1000 h	316 kWh
EPREL Registration Number	473300


Product Data			
Order product name	CDM ELITE TMW 315/930/U/O EU		
Full product name	CDM ELITE TMW 315/930/U/O EU		
Full product code	871829113956000		
Order code	928601167131		
Material Nr. (12NC)	928601167131		
Local order code	CDMELITE315930		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8727900862133		
Numerator - Packs per outer box	12		
EAN/UPC - Case	8718291139577		


Dimensional drawing




Product	D	D	С
CDM ELITE TMW 315/930/U/O EU	1.5 inch	38 mm	193 mm

Photometric data









Light Distribution Diagram - CDM ELITE TMW 315/930/U/O EU

Spectral Power Distribution Colour - CDM ELITE TMW 315/930/U/O EU

MASTERColour CDM-T Elite MW

Lifetime





Life Expectancy Diagram - CDM ELITE TMW 315/930/U/O EU

Lumen Maintenance Diagram - CDM ELITE TMW 315/930/U/O EU



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.