



Pulse Start Metal Halide Standard

MS400/U/PS 6/1

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	na [Not Applicable]
Life to 50% Failures (Nom)	20,000 hour(s)
Light Technical	
Color Code	640 [CCT of 4000K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	385
Chromaticity Coordinate Y (Nom)	390
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90 lm/W


Color rendering index (CRI)	65
Operating and Electrical	
Lamp Current (Nom)	3.25 A
Voltage (Nom)	135 V
Voltage (Nom)	135 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED37

Pulse Start Metal Halide Standard

Approval and Application	
Mercury (Hg) Content (Max)	42.0 mg
Product Data	
Order product name	MS400/U/PS 6PK
Full product name	MS400/U/PS 6/1
Order code	232835

Material Nr. (12NC)	928601179001
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677232832
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677232837

Dimensional drawing



Product	D	C (max)
MS400/U/PS 6PK	4.625 inch	11.5 inch

