



Fortimo LED linear light module

Fortimo LED LLM 1100/740 8W Gen4

The Fortimo LED linear light module (LLM) system represents a breakthrough in energy-efficient LED lighting for urban and residential applications. Cutting-edge LED technology ensures peak performance, delivering energy savings with Constant Light Output without compromising on light quality and comfort. Fortimo LED LLM offers a diffused white light LED alternative to traditional frosted light sources such as (compact) fluorescent, high-pressure mercury (HPL) and high-pressure sodium (SON) lamps. Designed primarily for residential outdoor lighting applications, this reliable, upgradeable solution is also suitable for many professional indoor applications. Fortimo LED LLM is a Green Product, contains no mercury and is fully RoHS-compliant.

Product data


General Information		Operating and Electrical	
Lighting Technology	LED	Power Consumption	8 W
Light Technical		Temperature	
Color Code	740 [CCT of 4000K]	Ambient temperature range	-20 °C to 55 °C
Luminous Flux	1,100 lumen	T-Case Lifetime (Nom)	65 °C
Color Designation	Neutral White	T-Case Maximum (Nom)	75 °C
Color Consistency Initial	5	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	130 lm/W	Approval and Application	
Color rendering index (CRI)	73	Approval Marks	CE marking ENEC certificate RoHS compliance REACH compliance
LLMF At End Of Nominal Lifetime (Nom)	80 %		

Fortimo LED linear light module

Product Data	
Full product code	871869643065100
Order product name	Fortimo LED LLM 1100/740 8W Gen4
Order code	929000941506
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

Material Nr. (12NC)	929000941506
Full product name	Fortimo LED LLM 1100/740 8W Gen4
EAN/UPC - Case	8718696430668
EAN/UPC - Product/Case	8718696430651

Dimensional drawing



Product	D1	C1	A1	A2	B1
Fortimo LED LLM 1100/740 8W Gen4	4.5 mm	40.5 mm	230.0 mm	214.5 mm	43.0 mm

