



CertaDrive LED linear drivers

CertaDrive 40W 360mA 110V 230V

The new CertaDrive non-isolated single current range is designed for basic lighting and perfect for high volume applications. The range offers a popular vout/lout mix, small dimensions and 50K hours lifetime at Tcase-life. The range consists of versions that are suitable for DC emergency operation and standard versions without this feature. For those customers that prefer more flexibility, the CertaDrive dipswitch versions, with four possible output currents, may be of interest.

Product data

General Information	
Lighting Technology	LED
Operating and Electrical	
Output Current (Max)	360 mA
Output Power (Max)	42 W
Output Power (Min)	29 W
Output Current (Min)	360 mA
Output Voltage (Max)	116 V
Output Voltage (Min)	80 V
Mechanical and Housing	
Housing	CertaDrive Linear 195mm

Product Data	
Order product name	CertaDrive 40W 360mA 110V 230V
Full product name	CertaDrive 40W 360mA 110V 230V
Full product code	871869649176800
Order code	929000974906
Material Nr. (12NC)	929000974906
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696491768
Numerator - Packs per outer box	20
EAN/UPC - Case	8718696491775