

# **T8**

# 10T8/48-3500 IF 10/1 TAA/NAFTA

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

### **Product data**

General Information					
Cap-Base	G13 [Medium Bi-Pin Fluorescent]				
Nominal lifetime	50,000 hour(s)				
Switching Cycle	50,000				
Lighting Technology	LED				
EU RoHS compliant	Yes				
Light Technical					
Color Code	835 [CCT of 3500K]				
Beam Angle (Nom)	180 degree(s)				
Luminous Flux	1,500 lm				
Color Designation	White (WH)				
Correlated Color Temperature (Nom)	3500 K				
Luminous Efficacy (rated) (Nom)	150.00 lm/W				
Color Consistency	<6				
Color rendering index (CRI)	82				
LLMF At End Of Nominal Lifetime (Nom) 70 %					
Operating and Electrical					
Line Frequency	50 to 60 Hz				


Input Frequency	50 to 60 Hz			
Power Consumption	10 W			
Starting Time (Nom)	0.5 s			
Warm-up time to 60% light	0.5 s			
Power Factor (Fraction)	0.9			
Voltage (Nom)	120-277, 347 V			
UL Type	Type A - works on ballast			
Temperature				
Ambient temperature range	-4 °F to 113 °F			
T-Case Maximum (Nom)	104 °F			
Controls and Dimming				
Dimmable	No			
Mechanical and Housing				
Bulb Material	Plastic			
Product Length	47-1/4 inch			
Bulb Shape	Tube, double-ended			
·				

Datasheet, 2023, August 2 data subject to change

Approval and Application	
Approval and Application	
Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC
	compliance
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard
Product Data	
Order product name	10T8/48-3500 IF 10/1 TAA/NAFTA


Full product name	10T8/48-3500 IF 10/1 TAA/NAFTA
Order code	469577
Material Nr. (12NC)	929001124084
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677472610
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677469578


# Dimensional drawing



Product	D1	D2	A1	A2	А3
10T8/48-3500 IF 10/1 TAA/	25.68 mm	28 mm	1,198.0 mm	1,205.0 mm	1,212.0 mm
NAFTA					


## Photometric data






Spectral Power Distribution Colour - 10T8/48-3500 IF 10/1 TAA/NAFTA


General uniform lighting - 10T8/48-3500 IF 10/1 TAA/NAFTA



Light Distribution Diagram - 10T8/48-3500 IF 10/1 TAA/NAFTA

### Lifetime





Lumen Maintenance Diagram - 10T8/48-3500 IF 10/1 TAA/NAFTA

Life Expectancy Diagram - 10T8/48-3500 IF 10/1 TAA/NAFTA

