



# MasterClass LEDtube InstantFit T8

## 10T8/48-3500 IF 10/1 TAA/NAFTA

The Masterclass LED Type A - Ballast Driven (Plug and Play) InstantFit TLED is a great LED solution suitable for replacing T8 fluorescent lamps, using an existing ballast. Specific lamps can also be used on Philips Xitanium driver for Type C applications.

### Product data

General Information		Starting Time (Nom)		0.5 s
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]	Warm Up Time to 60% Light (Nom)	0.5 s	
Main Application	Industrial	Power Factor (Nom)	0.9	
Nominal Lifetime (Nom)	50000 h	Voltage (Nom)	120-277, 347 V	
Switching Cycle	50000X	<b>Temperature</b>		
B50L70	50000 h	T-Ambient (Max)	45 °C	
<b>Light Technical</b>		T-Ambient (Min)	-20 °C	
Color Code	835 [ CCT of 3500K]	T-Storage (Max)	65 °C	
Luminous Flux (Nom)	1500 lm	T-Storage (Min)	-40 °C	
Luminous Flux (Rated) (Nom)	1500 lm	T-Case Maximum (Nom)	40 °C	
Correlated Color Temperature (Nom)	3500 K	<b>Controls and Dimming</b>		
Color Consistency	<6	Dimmable	No	
Color Rendering Index (Nom)	82	<b>Mechanical and Housing</b>		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Length	1200 mm	
<b>Operating and Electrical</b>		<b>Approval and Application</b>		
Input Frequency	50 to 60 Hz	Energy Saving Product	Yes	
Power (Rated) (Nom)	10 W			
Lamp Current (Nom)	140 mA			

# MasterClass LEDtube InstantFit T8


Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-

## Product Data

Order product name	10T8/48-3500 IF 10/1 TAA/NAFTA
EAN/UPC - Product	046677472610

Order code	929001124084
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001124084
Net Weight (Piece)	0.001 kg



## Dimensional drawing




LEDtube 1200mm 12W G13/835

Product	D1	D2	A1	A2	A3
10T8/48-3500 IF 10/1 TAA/NAFTA	25.68 mm	28 mm	1198.0 mm	1205.0 mm	1212.0 mm

## Photometric data



LEDtube 1200mm 12W G13 835 1500lm



# MasterClass LEDtube InstantFit T8

## Lifetime

