



T8

10T8/48-4000 IF 10/1 TAA/NAFTA

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux (Nom)	1600 lm
Correlated Color Temperature (Nom)	4000 K
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	10 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s

UL Type	Type A - works on ballast Type C - works with dedicated LED driver Type A+C - works with both ballasts and the LED driver
Power Factor (Nom)	0.9
Voltage (Nom)	120-277, 347 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1200 mm

T8

Approval and Application


Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Certifications	DLC Standard

Product Data

Order product name	10T8/48-4000 IF 10/1 TAA/NAFTA
--------------------	--------------------------------

EAN/UPC - Product	046677472627
Order code	929001124184
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001124184
Net Weight (Piece)	0.001 kg



Dimensional drawing



LEDtube 1200mm 12W G13/840

Product	D1	D2	A1	A2	A3
10T8/48-4000 IF 10/1 TAA/NAFTA	25.68 mm	28 mm	1198.0 mm	1205.0 mm	1212.0 mm


Photometric data



General Uniform Lighting



LEDtube 1200mm 12W G13 840 1600lm

LEDtube 1200mm 12W G13 840 1600lm



LEDtube 1200mm 12W G13 840 1600lm

Lifetime



LEDtube HF 1500mm 26W G5 T5

LEDtube 1200mm 14-32W G13

