

PHILIPS

Eco passport

LED 6.5W 310mm S19 WW ND 1CT/4

Lineares Tubulares LED

Philips LEDtube integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplamping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.



Our Eco passport

A Signify lidera o caminho para vidas mais luminosas e um mundo melhor. Como parte do processo de design, inovamos para reduzir o impacto ambiental e trazer benefícios alargados para as zonas do mundo onde desenvolvemos a nossa atividade.

Sabemos que isto também é importante para si. Desenvolvemos um passaporte Eco que explica o desempenho ambiental e social dos nossos produtos em oito Áreas de Foco Sustentáveis, desenvolvidas através do nosso processo de Design Sustentável desde 1994.



Energy

- Regulável: Não
- Etiqueta de Eficiência Energética (EEL): A+
- Power (Rated) (Nom): 6.5 W




Circularity

- Vida útil nominal (Nom.): 15000 h



Packaging

- SAP Weight Paper Unit (Case): 0,221 kg
- SAP Weight Paper Unit (Piece): 0,024 kg



Substances

- Em conformidade com RoHS da UE: Sim



Weight & Materials

- Peso líquido (Peça): 0,076 kg

Energy efficiency ranking / External awards



Leitura adicional em:
<https://www.philips.com/a-w/about/sustainability/sustainable-planet/green-products-and-green-innovation.html>

© 2020 Signify Holding. All rights reserved.