

Other LEDtube

LED 6.5W 310mm S19 WW ND 1CT/4

Philips LEDtube integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplampping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

Product data

General Information	
Cap-Base	S19 [S19]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	480 lm
Correlated Color Temperature (Nom)	2700 K
Color Consistency	<6
Color Rendering Index (Nom)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	6.5 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	45 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	300 mm

Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	7 kWh


Product Data	
Full product code	871869641985400

Other LEDtube

Order product name	LED 6.5W 310mm S19 WW ND 1CT/4
EAN/UPC - Product	8718696419854
Order code	929001126730
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

Material Nr. (12NC)	929001126730
Net Weight (Piece)	0.076 kg



Dimensional drawing



Product	C	D
LED 6.5W 310mm S19 WW ND 1CT/4	310 mm	38 mm

TLED T8 Diffuse 220V 6W-60W 2700K S19 ND


Photometric data



© 2020 Philips Lighting B.V. All rights reserved. Philips Lighting B.V.

LEDtube 310mm 6.5W S19 827 480lm ND

LEDtube 310mm 6.5W S19 827 480lm ND



LEDtube 310mm 6.5W S19 827 480lm ND

Other LEDtube

