

Essential LEDtube

LEDtube 1200mm16W765 T8 CN I G

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Light Technical	
Colour Code	765 [CCT of 6,500 K]
Technical Beam Angle (Nom)	240 °
Lamp Luminous Flux 25°C EL (Nom)	1600 lm
Colour Temperature, horizontal (Nom)	6500 K
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	73
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	16 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.5
Voltage (Nom)	220-240 V


Temperature	
T ambient (max.)	45 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product length	1200 mm
Approval and Application	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Suitable for accent lighting	No
Approval marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh
Product Data	
Full product code	694793910548900
Order product name	LEDtube 1200mm16W765 T8 CN I G

Essential LEDtube

EAN/UPC – product	6947939105489
Order code	929001127510
Numerator – quantity per pack	1
Numerator – packs per outer box	20

Material no. (12NC)	929001127510
Net weight (piece)	0.222 kg


Dimensional drawing




LEDtube 1200mm 16W 765

Product	D1	D2	A1	A2	A3
LEDtube 1200mm16W765	25.68	28 mm	1198.0	1205.0	1212.0
T8 CN I G	mm		mm	mm	mm

Photometric data




General Information 11 Photometry 11 Page 11



LEDtube 1200mm 16W 765 T8 CN I G



LEDtube 1200mm 16W 765 T8 CN I G



LEDtube 16W G13 765 CN I G



Essential LEDtube

Lifetime




LEDtube 15K FailureRate

LEDtube 15K



LEDtube 15K LumenVsTc

LEDtube 15K LifetimeVsTc



LEDtube 15K

Essential LEDtube

