



Essential LED tubes T5 Mains

MASTER LEDtube 1200mm 13W865 G5 I

The Essential LEDtube T5 is an affordable LED solution suitable for replacing T5 fluorescent lamps. Thanks to a unique design, Philips Essential LED tube T5 Mains can be directly installed in luminaires operating on mains power connection. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G5
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	1,600 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	123.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	
Input Frequency	50 to 60 Hz
Power Consumption	13 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	33 V

Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	50 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	1,200 mm
Bulb Shape	T5


Approval and Application	
Energy Saving Product	Yes

Essential LED tubes T5 Mains

Suitable For Accent Lighting	No
Approval Marks	RoHS compliance KEMA Keur certificate CE marking
Energy Consumption kWh/1000 h	15 kWh
Product Data	
Order product name	MASTER LEDtube 1200mm 13W865 G5 I
Full product name	MASTER LEDtube 1200mm 13W865 G5 I
Full product code	694793910875600



Order code	10875600
Material Nr. (12NC)	929001131210
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6947939108756
Numerator - Packs per outer box	20
EAN/UPC - Case	6947939108763

Dimensional drawing



Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm 13W865 G5 I	15.8 mm	21.0 mm	1,148.0 mm	1,155.0 mm	1,162.0 mm

Photometric data



Light Distribution Diagram - MASTER LEDtube 1200mm 13W865 G5 I

General uniform lighting - MASTER LEDtube 1200mm 13W865 G5 I

Essential LED tubes T5 Mains

Photometric data



Spectral Power Distribution Colour - MASTER LEDtube 1200mm 13W865 G5

I

