



# MASTER LEDcandle DiamondSpark

## MASTER LEDcandle DT 4-25W E14 B38 CL\_AP

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

### Product data

General Information	
Cap base	E14 [ E14]
Red Dot Design Award winner mark	Reddot Design Award Winner 2016
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	4-25W

Light Technical	
Colour Code	822-827 [ tunable warm white]
Lamp Luminous Flux 25°C EL (Nom)	250 lm
Lamp Luminous Flux (Nom)	250 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	2200-2700 K

Lamp Luminous Efficacy EM (Nom)	65 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %


Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W
Lamp current (nom.)	25 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	0.7

# MASTER LEDcandle DiamondSpark

Voltage (Nom)	220-240 V
<b>Temperature</b>	
T-Case maximum (nom.)	85 °C
<b>Controls and Dimming</b>	
Dimmable	yes
<b>Mechanical and Housing</b>	
Bulb finish	Clear
<b>Approval and Application</b>	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	No

Energy Consumption kWh/1000 h	4 kWh
<b>Product Data</b>	
Full product code	871869645372800
Order product name	MASTER LEDcandle DT 4-25W E14 B38 CL_AP
EAN/UPC – product	8718696453728
Order code	929001139808
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001139808
Net weight (piece)	0.063 kg



## Dimensional drawing



LED DT 4-25W E14 2200-2700K B38 CL

Product	D	C
MASTER LEDcandle DT 4-25W E14 B38 CL_AP	38 mm	113 mm

## Photometric data



## MASTER LEDcandle DiamondSpark

