



MASTER LEDcandle

MASTER LEDlustre DT 4-25W E14 P48 CL

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

Product data

General Information		LLMF at end of nominal lifetime (nom.)	
Cap base	E14 [E14]		70 %
Nominal lifetime (nom.)	25000 h	Operating and Electrical	
Switching cycle	50000X	Input frequency	50 to 60 Hz
Technical type	4-25W	Power (Rated) (Nom)	4 W
Light Technical		Lamp current (nom.)	25 mA
Colour code	822-827 [tunable warm white]	Wattage equivalent	25 W
Luminous flux (nom.)	250 lm	Starting time (nom.)	0.5 s
Colour designation	Warm White (WW)	Warm-up time to 60% light (nom.)	instant full light
Correlated colour temperature (nom.)	2200-2700 K	Power factor (nom.)	0.7
Luminous efficacy (rated) (nom.)	65 lm/W	Voltage (Nom)	220-240 V
Colour consistency	<6	Temperature	
Color rendering index (nom.)	80	T-Case maximum (nom.)	85 °C

MASTER LEDcandle

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb finish	Clear
-------------	-------


Approval and Application

Energy efficiency label (EEL)	A+
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	4 kWh

Product Data

Full product code	871869645378000
Order product name	MASTER LEDlustre DT 4-25W E14 P48 CL
EAN/UPC – product	8718696453780
Order code	45378000
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001140002
Net weight (piece)	0.072 kg

Dimensional drawing




LED DT 4-25W E14 P48 CL


Product

MASTER LEDlustre DT 4-25W E14 P48 CL

Photometric data



SDLD_LEDLSR_0023-Light distribution diagram



MASTER LEDcandle

