



# MASTER LEDcandle

## MASTER LEDlustre DT 6-40W E14 P48 CL

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

### Product data

General Information	
Base	E14 [ E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	6-40W
Light Technical	
Color Code	822-827 [ tunable warm white]
Initial lumen (Nom)	470 lm
Color Designation	Warm White (WW)
Luminous Efficacy (rated) (Nom)	75 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	6 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	95 °C

# MASTER LEDcandle

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Bulb Finish	Clear
-------------	-------


## Approval and Application

Energy Efficiency Label (EEL)	A+
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	6 kWh

## Product Data

Order product name	MASTER LEDlustre DT 6-40W E14 P48 CL
EAN/UPC - Product	8718696453582
Order code	304014
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001140602
Net Weight (Piece)	0.072 kg

## Dimensional drawing




LED DT 6-40W E14 P48 CL

## Product

MASTER LEDlustre DT 6-40W E14 P48 CL

## Photometric data



## MASTER LEDcandle

