



MASTER LEDcandle DiamondSpark

MASTER LEDcandle DT 6-40W B22 B38 CL

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

Product data

General Information	
Cap base	B22 [B22]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	6-40W
Light Technical	
Colour Code	822-827 [tunable warm white]
Lamp Luminous Flux 25°C EL (Nom)	470 lm
Colour Designation	Warm white (WW)
Lamp Luminous Efficacy EM (Nom)	75 lm/W
Colour consistency	<6

Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	6 W
Lamp current (nom.)	35 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V

MASTER LEDcandle DiamondSpark

Temperature	
T-Case maximum (nom.)	95 °C
Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Bulb finish	Clear
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	6 kWh

Product Data	
Full product code	871869645362900
Order product name	MASTER LEDcandle DT 6-40W B22 B38 CL
EAN/UPC – product	8718696453629
Order code	45362900
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001140802
Net weight (piece)	0.063 kg


Dimensional drawing



Candle B38 220-240V 6W-40W 2700K B22 DT

Product	D	C
MASTER LEDcandle DT 6-40W B22 B38 CL	38 mm	111 mm

Photometric data



MASTER LEDcandle DiamondSpark

