



CorePro LEDcandle

Corepro Candle ND 4-25W E14 827 B35 CL

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap-Base	E14 [E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	4-25W

Light Technical	
Colour Code	827 [CCT of 2700K]
Luminous Flux (Nom)	250 lm
Colour Designation	Warm White (WW)
Colour Temperature, horizontal (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	62.50 lm/W
Color Consistency	<6
Colour Rendering Index horiz (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	75 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear


Approval and Application	
Energy Efficiency Label	A+
Energy Consumption kWh/1000 h	4 kWh

Product Data	
Full product code	871869650757500
Order product name	Corepro Candle ND 4-25W E14 827 B35 CL
EAN/UPC - Product	8718696507575
Order code	50757500
Numerator - Quantity Per Pack	1

CorePro LEDcandle

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001142202
Net Weight (Piece)	0.040 kg



Dimensional drawing



LED ND 4-25W E14 827 220-240V B35 CL


Product
Corepro Candle ND 4-25W E14 827 B35 CL

Photometric data



CorePro LEDcandle 4-25W E14 827 CL B35

CorePro LEDcandle 4-25W E14 827 CL B35




SDPO_LEDCL_0003-Spectral Power distribution

CorePro LEDcandle

Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

