



# CorePro LEDcandle

## Corepro Lustre ND 4-25W E27 827 P45 CL

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

### Product data

General Information	
Cap base	E27 [ E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	4-25W

Light Technical	
Colour code	827 [ CCT of 2,700 K]
Luminous flux (nom.)	250 lm
Colour designation	Warm White (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	62.50 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W
Lamp current (nom.)	35 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s

Power factor (nom.)	0.4
Voltage (Nom)	220-240 V

Temperature	
T-Case maximum (nom.)	75 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb finish	Clear


Approval and Application	
Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	4 kWh

Product Data	
Full product code	871869650767400
Order product name	Corepro Lustre ND 4-25W E27 827 P45 CL
EAN/UPC – product	8718696507674
Order code	50767400
Numerator – quantity per pack	1
Numerator – packs per outer box	10

# CorePro LEDcandle

Material no. (12NC)	929001142402
Net weight (piece)	0.040 kg



## Dimensional drawing



LED ND 4-25W E27 827 220-240V P45 CL


Product	D	C
Corepro Lustre ND 4-25W E27 827 P45 CL	45 mm	87 mm

## Photometric data



CorePro LEDlustre 4-25W E27 827 CL P45

CorePro LEDlustre 4-25W E27 827 CL P45




SDPO\_LEDLSR\_0003-Spectral Power distribution

# CorePro LEDcandle

## Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

