

MASTER VALUE LEDs pot LV

MASTER LED 5.5-50W 4000K MR16 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU5.3
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	24 degree(s)
Luminous Flux	450 lm
Luminous Intensity (Nom)	1,800 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	82.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

MASTER VALUE LEDspot LV

LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	5.5 W
Lamp Current (Nom)	640 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V

Temperature

T-Case Maximum (Nom)	95 °C

Controls and Dimming

Dimmable	No

Mechanical and Housing

Bulb Shape	MR16


Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh

Product Data


Order product name	MASTER LED 5.5-50W 4000K MR16 24D
Full product name	MASTER LED 5.5-50W 4000K MR16 24D
Full product code	871869647609300
Order code	929001146808
Material Nr. (12NC)	929001146808
Local order code	5.5WMR16CW24D
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696476093
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696476109

Dimensional drawing




Product	D	C
MASTER LED 5.5-50W 4000K MR16 24D	50.2 mm	49 mm

Photometric data



General uniform lighting - MASTER LED 5.5-50W 4000K MR16 24D



Light Distribution Diagram - MASTER LED 5.5-50W 4000K MR16 24D

MASTER VALUE LEDspot LV

© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com
2024, February 2 - data subject to change