



MASTER VALUE LEDs pot LV

MASTER LED 4-35W 2700K MR16 24D

Philips MASTER VALUE MR16 is the series of Low Voltage (12VAC) Halogen MR16 replacements. Not only does it employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V Halogen electronic transformers. It also delivers beam intensity which is equivalent to the 50W Philips Halogen MR16 lamps. The form-factor of Philips MASTER Value LED MR16 guarantees a 100% form on the back-side of the lamp (exact form with Halogen lamps.)

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- · Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	24 degree(s)
Luminous Flux	240 lm
Luminous Intensity (Nom)	1,000 cd
Color Designation	Warm White (WW)

Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	65.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	220 lm
Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	4 W
Lamp Current (Nom)	520 mA
Wattage Equivalent	35 W


Datasheet, 2023, November 15 data subject to change

MASTER VALUE LEDspot LV

Starting Time (Nom)	0.5 s	
Warm-up time to 60% light	instant full light s	
Power Factor (Fraction)	0.7	
Voltage (Nom)	12 V	
Temperature		
T-Case Maximum (Nom)	65 °C	
Controls and Dimming		
Dimmable	No	
Mechanical and Housing		
Bulb Shape	MR16 [2inch/50mm]	
Approval and Application		
Suitable For Accent Lighting	Yes	


Energy Consumption kWh/1000 h	4 kWh
Product Data	
Order product name	MASTER LED 4-35W 2700K MR16 24D
Full product name	MASTER LED 4-35W 2700K MR16 24D
Full product code	871869647619200
Order code	929001147408
Material Nr. (12NC)	929001147408
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696476192
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696476208

Dimensional drawing



Product	D	С
MASTER LED 4-35W 2700K MR16 24D	50 mm	49 mm

Photometric data





Light Distribution Diagram - MASTER LED 4-35W 2700K MR16 24D

Spectral Power Distribution Colour - MASTER LED 4-35W 2700K MR16 24D

MASTER VALUE LEDspot LV



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.