



MASTER VALUE LEDs

pot LV

MASTER LED 4-35W 3000K MR16 24D

Philips MASTER VALUE MR16 is the series of Low Voltage (12VAC) Halogen MR16 replacements. Not only does it employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V Halogen electronic transformers. It also delivers beam intensity which is equivalent to the 50W Philips Halogen MR16 lamps. The form-factor of Philips MASTER Value LED MR16 guarantees a 100% form on the back-side of the lamp (exact form with Halogen lamps.)

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU5.3
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	24 degree(s)
Luminous Flux	240 lm
Luminous Intensity (Nom)	1,000 cd
Color Designation	White (WH)

Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	65.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	225 lm


Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Power Consumption	3.4 W
Lamp Current (Nom)	520 mA
Wattage Equivalent	35 W

MASTER VALUE LEDspot LV

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	MR16
Approval and Application	
Suitable For Accent Lighting	Yes


Energy Consumption kWh/1000 h	4 kWh
Product Data	
Order product name	MASTER LED 4-35W 3000K MR16 24D
Full product name	MASTER LED 4-35W 3000K MR16 24D
Full product code	871869647625300
Order code	929001147708
Material Nr. (12NC)	929001147708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696476253
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696476260

Dimensional drawing




Product	D	C
MASTER LED 4-35W 3000K MR16 24D	50 mm	49 mm

Photometric data



Light Distribution Diagram - MASTER LED 4-35W 3000K MR16 24D



Spectral Power Distribution Colour - MASTER LED 4-35W 3000K MR16 24D

MASTER VALUE LEDspot LV

