



MASTER LEDbulb

MASTER LEDbulb DT 6-40W B22 A60 CL

MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. It is particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 or a B22 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimises maintenance cost without any compromise on light quality.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data



General Information		Colour rendering index (CRI)	
Cap base	B22 [B22]	LLMF at end of nominal lifetime (nom.)	70 %
Nominal lifetime	25,000 h	Operating and Electrical	
Switching Cycle	50,000	Line Frequency	50 to 60 Hz
Lighting Technology	LED	Input frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power Consumption	6 W
Light Technical		Lamp current (nom.)	37 mA
Colour Code	822-827 [tunable warm white]	Wattage equivalent	40 W
Luminous Flux	470 lm	Starting time (nom.)	0.5 s
Colour designation	Warm White (WW)	Warm-up time to 60% light	Instant full light s
Luminous efficacy (rated) (nom.)	78.00 lm/W	Power Factor (Fraction)	0.7
Colour consistency	<6		

MASTER LEDbulb

Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	85 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	A60 [A 60 mm]
Approval and Application	
Suitable for accent lighting	No
Energy consumption kWh/1,000 hours	6 kWh

EyeComfort	Yes
Product Data	
Order product name	MAS LEDbulb DT 6-40W B22 A60 CL
Full product name	MASTER LEDbulb DT 6-40W B22 A60 CL
Full EOC	871869648130100
Order code	48130100
Material no. (12 NC)	929001150602
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696481301
Numerator – packs per outer box	10
EAN/UPC - Case	8718696481318

Dimensional drawing




Product	D	C
MAS LEDbulb DT 6-40W B22 A60 CL	60 mm	110 mm

Product
MAS LEDbulb DT 6-40W B22 A60 CL

MASTER LEDbulb

Photometric data



Light Distribution Diagram - MAS LEDbulb DT 6-40W B22 A60 CL

Spectral Power Distribution Colour - MAS LEDbulb DT 6-40W B22 A60 CL

