



MASTER LEDbulb

MASTER LEDbulb DT 8.5-60W B22 A60 CL

MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. It is particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 or a B22 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimises maintenance cost without any compromise on light quality.

Product data

General Information	
Cap base	B22 [B22]
Nominal lifetime (nom.)	25000 h
Switching cycle	50000X
Technical type	8.5-60W
Light Technical	
Colour code	822-827 [tunable warm white]
Luminous flux (nom.)	806 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	2200-2700 K
Luminous efficacy (rated) (nom.)	94 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	8.5 W

Lamp current (nom.)	45 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	110 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Clear
Approval and Application	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes


MASTER LEDbulb

Suitable for accent lighting	No
Energy Consumption kWh/1000 h	9 kWh
Product Data	
Full product code	871869648134900
Order product name	MASTER LEDbulb DT 8.5-60W B22 A60 CL
EAN/UPC – product	8718696481349

Order code	48134900
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001150732
Net weight (piece)	0.076 kg

Warnings and Safety

Dimensional drawing



LED DT 9-60W B22 A60 CL

Product	D	C
MASTER LEDbulb DT 8.5-60W B22 A60 CL	60 mm	110 mm

Photometric data

