

PHILIPS

Eco passport

MAS LEDbulb DT 6-40W E27 A60 CL MASTER LEDbulb

MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. It is particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 or a B22 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimises maintenance cost without any compromise on light quality.



Our Eco passport



Energy

- Dimmable: yes
- Energy efficiency label (EEL): A+
- Lamp Luminous Efficacy EM (Nom): 78.00 lm/W
- Power (Rated) (Nom): 6 W



Circularity

- Nominal lifetime (nom.): 25000 h



Packaging

- SAP Weight Paper Unit (Case): 0.415 kg
- SAP Weight Paper Unit (Piece): 0.020 kg



Substances

- EU RoHS compliant: No



Weight & Materials

- Net weight (piece): 0.076 kg

Energy efficiency ranking / External awards

