



CorePro LEDcandle

CorePro lustre ND 4-25W E14 827 P45 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.


Product data

General Information		Power factor (nom.)	
Cap base	E14 [E14]		0.4
Nominal lifetime (nom.)	15000 h	Voltage (Nom)	220-240 V
Switching cycle	50000X	Temperature	
Technical type	4-25W	T-Case maximum (nom.)	75 °C
Light Technical		Controls and Dimming	
Colour code	827 [CCT of 2,700 K]	Dimmable	no
Luminous flux (nom.)	250 lm	Mechanical and Housing	
Colour designation	Warm white (WW)	Bulb finish	Frosted
Correlated colour temperature (nom.)	2700 K	Approval and Application	
Luminous efficacy (rated) (nom.)	62.50 lm/W	Energy efficiency label (EEL)	A+
Colour consistency	<6	Energy Consumption kWh/1000 h	4 kWh
Color rendering index (nom.)	80	Product Data	
LLMF at end of nominal lifetime (nom.)	70 %	Full product code	871829178703700
Operating and Electrical		Order product name	CorePro lustre ND 4-25W E14 827 P45 FR
Input frequency	50 to 60 Hz	EAN/UPC – product	8718291787037
Power (Rated) (Nom)	4 W	Order code	78703700
Lamp current (nom.)	35 mA	Local Code	CPL4E14827FR
Wattage equivalent	25 W	Numerator – quantity per pack	1
Starting time (nom.)	0.5 s		
Warm-up time to 60% light (nom.)	0.5 s		

CorePro LEDcandle

Numerator – packs per outer box	10
Material no. (12NC)	929001157502
Net weight (piece)	0.040 kg



Dimensional drawing



LED ND 4-25W E14 827 220-240V P45 FR


Product	D	C
CorePro lustre ND 4-25W E14 827 P45 FR	45 mm	88 mm

Photometric data



CorePro LEDlustre 4-25W E14 827 FR P45

CorePro LEDlustre 4-25W E14 827 FR P45




SDPO_LEDLSR_0003-Spectral Power distribution

CorePro LEDcandle

Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

