



CorePro LEDcandle

CorePro lustre ND 4-25W E27 827 P45 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	4-25W

Light Technical	
Colour Code	827 [CCT of 2,700 K]
Lamp Luminous Flux 25°C EL (Nom)	250 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	62.50 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W
Lamp current (nom.)	35 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s

Power factor (nom.)	0.4
Voltage (Nom)	220-240 V

Temperature	
T-Case maximum (nom.)	75 °C

Controls and Dimming	
Dimmable	no

Mechanical and Housing	
Bulb finish	Frosted

Approval and Application	
Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	4 kWh

Product Data	
Full product code	871829178705100
Order product name	CorePro lustre ND 4-25W E27 827 P45 FR
EAN/UPC – product	8718291787051
Order code	929001157602
Numerator – quantity per pack	1
Numerator – packs per outer box	10

CorePro LEDcandle

Material no. (12NC)	929001157602
Net weight (piece)	0.040 kg



Dimensional drawing



Product	D	C
CorePro lustre ND 4-25W E27 827 P45 FR	45 mm	87 mm


LED ND 4-25W E27 827 220-240V P45 FR

Photometric data



CorePro LEDlustre 4-25W E27 827 FR P45


CorePro LEDlustre 4-25W E14 827 FR P45



SDPO_LEDLSR_0003-Spectral Power distribution

CorePro LEDcandle

Lifetime



LEDbulb 60W E14 827 FR B38

LEDbulb 60W E14 827 FR B38

