



CorePro LED candles and lusters

CorePro lustre ND 4-25W E27 827 P45 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Base	E27 [E27]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	4-25W
Light Technical	
Color Code	827 [CCT of 2700K]
Initial lumen (Nom)	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	62.50 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W

Lamp Current (Nom)	35 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	4 kWh

CorePro LED candles and lusters

Product Data

Order product name	CorePro lustre ND 4-25W E27 827 P45 FR
EAN/UPC - Product	8718291787051
Order code	304394
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001157602
Net Weight (Piece)	0.040 kg



Dimensional drawing



Product	D	C
CorePro lustre ND 4-25W E27 827 P45 FR	45 mm	87 mm


LED ND 4-25W E27 827 220-240V P45 FR

Photometric data



CorePro LEDlustre 4-25W E27 827 FR P45

CorePro LEDlustre 4-25W E14 827 FR P45




SDPO_LEDLSR_0003-Spectral Power distribution

CorePro LED candles and lusters

Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

