

**PHILIPS**

Eco passport

## MASTER LEDcandle DT 6-40W E27 B38 CL MASTER LEDcandle DiamondSpark

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.



### Our Eco passport



#### Energy

- Dimmable: yes
- Energy efficiency label (EEL): A+
- Luminous efficacy (rated) (nom.): 75 lm/W
- Power (Rated) (Nom): 6 W



#### Circularity

- Nominal lifetime (nom.): 25000 h



#### Packaging

- SAP Weight Paper Unit (Case): 0.205 kg
- SAP Weight Paper Unit (Piece): 0.014 kg



#### Substances

- EU RoHS compliant: No



#### Weight & Materials

- Net weight (piece): 0.063 kg

Energy efficiency ranking / External awards

