



Standard LED candles & lusters

LEDBulb 4-40W E27 6500K 220-240V P45

Standard LED candles are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving candles. They deliver huge energy savings and minimize maintenance costs. The Standard LED candle is the perfect candle for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

Product data

General Information		Operating and Electrical	
Cap-Base	E27 [E27]	Line Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	50 to 60 Hz
Switching Cycle	50,000	Power Consumption	4 W
Lighting Technology	LED	Lamp Current (Nom)	40 mA
EU RoHS compliant	Yes	Wattage Equivalent	40 W
		Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	865 [CCT of 6500K]	T-Case Maximum (Nom)	90 °C
Beam Angle (Nom)	150 degree(s)		
Luminous Flux	350 lm	Controls and Dimming	
Color Designation	Cool Daylight	Dimmable	No
Correlated Color Temperature (Nom)	6500 K		
Luminous Efficacy (rated) (Nom)	87.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Frosted
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

Standard LED candles & lusters


Bulb Shape	P45 [P 45mm]
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	LEDBulb 4-40W E27 6500K 220-240V P45
Full product name	LEDBulb 4-40W E27 6500K 220-240V P45
Full product code	871869678874500

Order code	929001161071
Material Nr. (12NC)	929001161071
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696788745
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696788752


Dimensional drawing

Product	D	C
LEDBulb 4-40W E27 6500K 220-240V P45	45 mm	87 mm


Photometric data



Spectral Power Distribution Colour - LEDBulb 4-40W E27 6500K 220-240V P45



General uniform lighting - LEDBulb 4-40W E27 6500K 220-240V P45



Light Distribution Diagram - LEDBulb 4-40W E27 6500K 220-240V P45

Standard LED candles & lusters

