



MASTER LEDspot LV AR111

MAS LEDspotLV D 11-50W 927 AR111 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimises maintenance cost without any reduction in brightness.

Product data

General Information	
Cap base	G53 [G53]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	40000 h
Switching cycle	50000X
Technical type	11-50W
Light Technical	
Colour code	927
Beam Angle (Nom)	24 °
Luminous flux (nom.)	560 lm
Luminous intensity (nom.)	2900 cd
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K


Luminous efficacy (rated) (nom.)	50.91 lm/W
Colour consistency	<3
Color rendering index (nom.)	90
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	560 lm
Operating and Electrical	
Power (Rated) (Nom)	11 W
Lamp current (nom.)	1300 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7

MASTER LEDspot LV AR111

Voltage (Nom)	12 V
Temperature	
T-Case maximum (nom.)	70 °C
Controls and Dimming	
Dimmable	yes
Approval and Application	
Energy efficiency label (EEL)	A
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	13 kWh

Product Data	
Full product code	871869651488700
Order product name	MAS LEDspotLV D 11-50W 927 AR111 24D
EAN/UPC – product	8718696514887
Order code	51488700
Local Code	MLED11AR112724N
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001169802
Net weight (piece)	0.160 kg



Dimensional drawing



LED D 11-50W 927 AR111 24D

Product
MAS LEDspotLV D 11-50W 927 AR111 24D


Photometric data





MASTER LEDspot LV AR111 50W G53 927 24D

MASTER LEDspot LV AR111

Photometric data



Lifetime



MASTER LEDspotLV AR111 75W G53 940 40D

MASTER LEDspotLV AR111 75W G53 940 40D

