



MASTER LEDspot LV AR111

MAS LEDspotLV D 15-75W 927 AR111 40D

With its new perfect-fit design, the Master LEDspot LV AR111 now works with most of G53 luminaires as a true retrofit solution. The lamp creates a brilliant visual effect for retail and hospitality applications such as shops, showrooms and galleries. The high quality light brings out the true colors in merchandise and emphasizes its beauty. It also lasts long, with a strong lumen and color maintenance. The beautifully designed lamp offers a well-defined beam with a multitude of beam angles to suit various applications. Not only does it employ the Philips patented solution to ensure it is compatible with a broad selection of standard 12V halogen electronic transformers, it also delivers high beam intensity which equivalent to halogen AR111 spots of 50W, 75W or 100W.

Product data


General Information		Color Consistency	
Cap-Base	G53 [G53]	Color rendering index (CRI)	<3
Nominal lifetime	40,000 hour(s)	LLMF At End Of Nominal Lifetime (Nom)	90
Switching Cycle	50,000	Luminous Flux in 90° Cone (Rated)	70 %
Lighting Technology	LED		
EU RoHS compliant	Yes		
Light Technical		Operating and Electrical	
Color Code	927	Line Frequency	- Hz
Beam Angle (Nom)	40 degree(s)	Input Frequency	- Hz
Luminous Flux	800 lm	Power Consumption	15 W
Luminous Intensity (Nom)	1,400 cd	Lamp Current (Nom)	1,800 mA
Color Designation	Warm White (WW)	Wattage Equivalent	75 W
Correlated Color Temperature (Nom)	2700 K	Starting Time (Nom)	0.5 s
Luminous Efficacy (rated) (Nom)	53.33 lm/W	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7

MASTER LEDspot LV AR111

Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	74 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	AR111
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	17 kWh

EyeComfort	Yes
Product Data	
Order product name	MAS LEDspotLV D 15-75W 927 AR111 40D
Full product name	MAS LEDspotLV D 15-75W 927 AR111 40D
Full product code	871869651500600
Order code	929001170402
Material Nr. (12NC)	929001170402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696515006
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696515013

Dimensional drawing




Product	D	C
MAS LEDspotLV D 15-75W 927 AR111 40D	111 mm	62 mm

Product
MAS LEDspotLV D 15-75W 927 AR111 40D


MASTER LEDspot LV AR111

Photometric data




Accent Lighting Spots - MAS LEDspotLV D 15-75W 927 AR111 40D

Light Distribution Diagram - MAS LEDspotLV D 15-75W 927 AR111 40D




Spectral Power Distribution Colour - MAS LEDspotLV D 15-75W 927 AR111 40D

Lifetime



Life Expectancy Diagram - MAS LEDspotLV D 15-75W 927 AR111 40D



Lumen Maintenance Diagram - MAS LEDspotLV D 15-75W 927 AR111 40D

MASTER LEDspot LV AR111

