

LED AR111

16AR111/LED/927/F40 DIM 12V FB 1PK 6/1

With an elegant new design, Philips MasterClass LED AR111 creates a brilliant visual effect. With excellent rendering of 90+ CRI and R9>50, colors stay vibrant and natural, enhancing the appeal of everything on display.


Product data

General Information	
Base	G53 [G53]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	40000 h
Switching Cycle	50000X
Technical Type	15-75W
Light Technical	
Color Code	927
Beam Angle (Nom)	40 °
Initial lumen (Nom)	740 lm
Luminous Intensity (Nom)	1400 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	55.33 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	740 lm
Operating and Electrical	
Power (Rated) (Nom)	15 W
Lamp Current (Nom)	1800 mA
Wattage Equivalent	75 W

Starting Time (Nom)	0.5 s	
Warm Up Time to 60% Light (Nom)	0.5 s	
Power Factor (Nom)	0.7	
Voltage (Nom)	12 V	
Temperature		
T-Case Maximum (Nom)	74 °C	
Controls and Dimming		
Dimmable	Yes	
Approval and Application		
Energy Efficiency Label (EEL)	Not applicable	
Suitable For Accent Lighting	Yes	
Energy Consumption kWh/1000 h	- kWh	
Product Data		
Order product name	16AR111/LED/927/F40 DIM 12V FB 1PK 6/1	
EAN/UPC - Product	046677460150	
Order code	460154	
Numerator - Quantity Per Pack	1	
Numerator - Packs per outer box	6	
Material Nr. (12NC)	929001170404	
Net Weight (Piece)	0.160 kg	


Datasheet, 2020, January 24 data subject to change


Dimensional drawing




Product	D	С
16AR111/LED/927/F40 DIM 12V FB 1PK 6/1	111 mm	62 mm

Photometric data






MASTER LEDspot LV AR111 75W G53 927 40D




SDPO_LEDspotL_0027-Spectral Power distribution

LED AR111

Lifetime





MASTER LEDspotLV AR111 75W G53 940 40D

MASTER LEDspotLV AR111 75W G53 940 40D



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.