



MASTER LEDspot LV AR111

MAS LEDspotLV D 15-75W 930 AR111 40D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimises maintenance cost without any reduction in brightness.

Product data


General Information		Operating and Electrical	
Cap-Base	G53 [G53]	Luminous Efficacy (rated) (Nom)	56.00 lm/W
Nominal lifetime	40,000 hour(s)	Color Consistency	<6
Switching Cycle	50,000	Color rendering index (CRI)	90
Lighting Technology	LED	LLMF At End Of Nominal Lifetime (Nom)	70 %
EU RoHS compliant	Yes	Luminous Flux in 90° Cone (Rated)	760 lm
Light Technical		Line Frequency	
Color Code	930 [CCT of 3000K]	Input Frequency	- Hz
Beam Angle (Nom)	40 degree(s)	Power Consumption	15 W
Luminous Flux	840 lm	Lamp Current (Nom)	1,800 mA
Luminous Intensity (Nom)	1,450 cd	Wattage Equivalent	75 W
Color Designation	White (WH)	Starting Time (Nom)	0.5 s
Correlated Color Temperature (Nom)	3000 K	Warm-up time to 60% light	instant full light s

MASTER LEDspot LV AR111

Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	74 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	AR111
Approval and Application	
Suitable For Accent Lighting	Yes



Energy Consumption kWh/1000 h	17 kWh
Product Data	
Order product name	MAS LEDspotLV D 15-75W 930 AR111 40D
Full product name	MAS LEDspotLV D 15-75W 930 AR111 40D
Full product code	871869651522800
Order code	929001170508
Material Nr. (12NC)	929001170508
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696515228
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696515235

Dimensional drawing



Product	D	C
MAS LEDspotLV D 15-75W 930 AR111 40D	111 mm	62 mm

Photometric data



Accent Lighting Spots - MAS LEDspotLV D 15-75W 930 AR111 40D

Light Distribution Diagram - MAS LEDspotLV D 15-75W 930 AR111 40D


MASTER LEDspot LV AR111

Photometric data




Spectral Power Distribution Colour - MAS LEDspotLV D 15-75W 930 AR111 40D

Lifetime



Life Expectancy Diagram - MAS LEDspotLV D 15-75W 930 AR111 40D



Lumen Maintenance Diagram - MAS LEDspotLV D 15-75W 930 AR111 40D

