



MASTER LEDspot LV AR111

MAS LEDspotLV D 20-100W 827 AR111 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimizes maintenance cost without any reduction in brightness.

产品数据


基本資訊		色彩一致性	
接口	G53 [G53]	演色性指數 (標稱)	<3
標稱使用時間 (標稱)	25000 h	標稱使用時間結束時的燈具流明維護係數 (標稱)	80
開關週期	50000X		
技術類型	20-100W		
照明科技		運作和電氣	
色碼	827 [CCT of 2700K]	Power (Rated) (Nom)	20 W
Beam Angle (Nom)	24 °	燈具電流 (標稱)	2400 mA
光通量 (標稱)	1300 lm	相等瓦數	100 W
光強 (標稱)	5800 cd	起始時間 (標稱)	0.5 s
色彩名稱	暖 白色 (WW)	至 60% 亮度的暖機時間 (標稱)	0.5 s
相關色溫 (標稱)	2700 K	功率因數 (標稱)	0.7
光效 (額定) (標稱)	65.00 lm/W	電壓 (標稱)	12 V

MASTER LEDspot LV AR111

溫度	
T 盒上限 (標稱)	80 °C
控制調光	
可調光	Yes
應用	
能源效益標籤 (EEL)	A
適合重點照明	Yes
能源消耗 kWh/1000 h	22 kWh

產品參數	
完整產品碼	871869670729600
訂購產品名稱	MAS LEDspotLV D 20-100W 827 AR111 24D
EAN/UPC - 產品	8718696707296
訂購代碼	929001170808
分子 - 各件數量	1
分子 - 每一外盒內件數	6
材質編號(12NC)	929001170808
淨重 (件)	0.360 kg


二维绘图




LED D 20-100W 827 AR111 24D

Product	D	C
MAS LEDspotLV D 20-100W 827 AR111 24D	111 mm	62 mm

光度数据



MASTER LEDspot LV AR111 100W G53 827 24D




MASTER LEDspot LV AR111

光度数据




SDPO_LEDspotL_0022-Spectral Power distribution

壽命



MASTER LEDspotLV AR111 100W G53 40D



MASTER LEDspotLV AR111 100W G53 40D

