



Led 3-Way

18A21/LED/827 3WAY ND 120V

Philips LED A-shape light bulb provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	18-100W
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	1600 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	88.88 lm/W
Color Consistency	ANSI
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Nom)	18 W
Lamp Current (Nom)	170 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s

Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	100 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Approval and Application	
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	18/8/5 kWh
Energy Certifications	Energy Star
Product Data	
Order product name	18A21/LED/827 3WAY ND 120V
EAN/UPC - Product	046677459161
Order code	929001174204
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001174204

Led 3-Way

Net Weight (Piece)	0.155 kg
--------------------	----------


Dimensional drawing




Bulb A21 120V 18-120W 1600lm 827 E26 ND

Product	D	C
18A21/LED/827 3WAY ND 120V	71.1 mm	134.6 mm


Photometric data



LEDbulb, Bulb A21 14W, 18W 2200-2700K



LEDlamps, A21 18W-100W 2700K 1600lm



LEDlamps, A21 18W-100W 2700K 1600lm

Led 3-Way

