



LED B11

7B12/LED/827-22/E26/DIM 120V

Philips LED B11 candles offer energy saving ambiance with the elegant effect of incandescent candles. These designs provides light in an omnidirectional manner, giving lighting designers a long life alternative to standard incandescent sources.

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	7-60W
Light Technical	
Color Code	822-827 [tunable warm white]
Luminous Flux (Nom)	500 lm
Color Designation	Warm White (WW)
Color Consistency	ANSI 2700K
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	7 W
Lamp Current (Nom)	65 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	0.9

Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	100 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	7 kWh
Energy Certifications	Energy Star
Product Data	
Order product name	7B12/LED/827-22/E26/DIM 120V
EAN/UPC - Product	046677458669
Order code	458661
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001182104

LED B11

Net Weight (Piece) 0.072 kg



Dimensional drawing



LED 7-60W E26 B12 CL DIM


Product	D	C
7B12/LED/827-22/E26/DIM 120V	38 mm	110 mm

Photometric data



LED Bulb Candle and Lustre 7W E26 B12 Clear 2700K

7-60 W E26 B12, F15 /822-827 CL



CorePro 822-827

LED B11

