PHILIPS

Lighting



Ecofit Ledtubes T8

LEDtube 1200mm 16W 765 T8 AP C G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	765 [CCT of 6500K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	1,600 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<7
Color rendering index (CRI)	73
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	16 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	60 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	1,200 mm
Bulb Shape	T8

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	RoHS compliance KEMA Keur certificate

Ecofit Ledtubes T8


Energy Consumption kWh/1000 h	16 kWh

Material Nr. (12NC)	929001184608
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696525036
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696525043

Product Data


Order product name	LEDtube 1200mm 16W 765 T8 AP C G
Full product name	LEDtube 1200mm 16W 765 T8 AP C G
Full product code	871869652503600
Order code	929001184608

Dimensional drawing




Product	D1	D2	A1	A2	A3	C	D
LEDtube 1200mm 16W 765 T8 AP C G	25.68 mm	28 mm	1,198 mm	1,205 mm	1,212 mm	1,212 mm	27.8 mm


Photometric data



General uniform lighting - LEDtube 1200mm 16W 765 T8 AP C G




Light Distribution Diagram - LEDtube 1200mm 16W 765 T8 AP C G




Spectral Power Distribution Colour - LEDtube 1200mm 16W 765 T8 AP C G

Ecofit Ledtubes T8


Lifetime




Life Expectancy Diagram - LEDtube 1200mm 16W 765 T8 AP C G




Life Expectancy Diagram - LEDtube 1200mm 16W 765 T8 AP C G



Life Expectancy Diagram - LEDtube 1200mm 16W 765 T8 AP C G



Lumen Maintenance Diagram - LEDtube 1200mm 16W 765 T8 AP C G



Lumen Maintenance Diagram - LEDtube 1200mm 16W 765 T8 AP C G

Ecofit Ledtubes T8



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com
2023, April 14 - data subject to change