



Ecofit Ledtubes T8

Suitable For Accent Lighting	No
Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
EyeComfort	Yes
LED Innovations	EyeComfort

Product Data



Order product name	LEDtube 600mm 8W 740 T8 AP C G
Full product name	LEDtube 600mm 8W 740 T8 AP C G

Full product code	871869652505000
Order code	52505000
Material Nr. (12NC)	929001184708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696525050
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696525067

Dimensional drawing


Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28 mm	588.5	595.5	602.5	602.5	27.8
8W 740 T8 AP C G	mm		mm	mm	mm	mm	mm

Photometric data



General uniform lighting - LEDtube 600mm 8W 740 T8 AP C G



Light Distribution Diagram - LEDtube 600mm 8W 740 T8 AP C G




Spectral Power Distribution Colour - LEDtube 600mm 8W 740 T8 AP C G

Ecofit Ledtubes T8


Lifetime




Life Expectancy Diagram - LEDtube 600mm 8W 740 T8 AP C G



Life Expectancy Diagram - LEDtube 600mm 8W 740 T8 AP C G



Life Expectancy Diagram - LEDtube 600mm 8W 740 T8 AP C G



Lumen Maintenance Diagram - LEDtube 600mm 8W 740 T8 AP C G

Lumen Maintenance Diagram - LEDtube 600mm 8W 740 T8 AP C G

Ecofit Ledtubes T8

